

**Electromagnetic compatibility
and Radio Spectrum Matters ERM
ERM TEST REPORT
288405-4-1**

Test Report

**Electromagnetic compatibility
and Radio spectrum Matters (ERM)**



Equipment Under Test: WiFi module

Model: WF111-A, WF111-E
WF121-A, WF121-E
WGM110A, WGM110E

Trade Mark: Silicon Labs / Bluegiga

Manufacturer/Customer: Silicon Laboratories Finland Oy
Bertel Jungin aukio 3
FI-02600, ESPOO
FINLAND

Tests have been performed according to the following standard(s)

Title of the standard	Reference standard	Version
Wideband transmission systems; Data transmission equipment operating in the 2,4 GHz ISM band and using wide band modulation techniques; Harmonised Standard covering the essential requirements of article 3.2 of Directive 2014/53/EU <i>- Partial testing, see test suite for details</i>	EN 300 328	V2.1.1

Date: 10 May 2017

Issued by: 
Emil Haverinen
Testing Engineer

Date: 10 May 2017

Checked by: 
Rauno Repo
Testing Engineer

Disclaimer

This document is issued by the Company under its General Conditions of service accessible at [http://www.sgs.com/terms and conditions.htm](http://www.sgs.com/terms_and_conditions.htm). attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein.

Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of Client's instructions, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law.

Unless otherwise stated the results shown in this test report refer only to the sample(s) tested and such sample(s) are retained for 90 days only. This document cannot be reproduced except in full, without prior approval of the Company.

GENERAL REMARKS	3
Disclaimer	3
TABLE OF CONTENTS.....	4
PRODUCT DESCRIPTION	5
Equipment under test (EUT).....	5
General description	5
Modifications incorporated in the EUT	5
Specifications of the EUT	5
Power requirements.....	5
Equipment category and characteristics	5
Peripherals	5
Photographs of the EUT.....	6
SUMMARY OF TESTING	7
Test conditions.....	7
Test suite.....	8
TEST RESULTS.....	9
Receiver Blocking	9
TEST EQUIPMENT	10

Equipment under test (EUT)

Model: WF111-A, WF111-E, WF121-A, WF121-E, WGM110A, WGM110E
 Trade Mark: Silicon Labs / Bluegiga
 Serial: -

General description

The equipment under test is a WiFi module. Model specific information is provided in the table below:

Model:	Description:	Rated RF Output power:	Receiver Category:
WF111-A, WF111-E	IEEE 802.11 b/g/n radio	+16 dBm	1
WF121-A, WF121-E	IEEE 802.11 b/g/n radio	+16 dBm	1
WGM110A, WGM110E	IEEE 802.11 b/g/n radio	+16 dBm	1

Modifications incorporated in the EUT

No modifications were made.

Specifications of the EUT

Highest antenna gain: 2.14 dBi (declared by the manufacturer)
 EUT dimensions: Smaller than 40 x 40 x 40 mm

Power requirements


Type: Supplied by the end product
 Rated voltage: Tested with 3.3 V
 Rated current: -
 Rated frequency: DC

Equipment category and characteristics

Operating Frequency Range (OFR): 2412 - 2472 MHz
 Channels: 13
 Channel separation: 5 MHz
 Channel bandwidth: 20 MHz
 Transmission technique: DSSS
 Modulation: CCK, QPSK, OFDM
 Geo-location capability: -

Peripherals

Test PC
 Evaluation board
 WiFi router

Photographs of the EUT**Photograph 1:** WF111**Photograph 2:** WF121**Photograph 3:** WGM110

Test conditions

The EUT was set into continuous transmit/receive mode to certain channel during the measurements.

Receiver blocking test was performed using two samples. One was set to continuously transmit and other one was set to receive continuously.

Performance of the receiver was monitored with software provided by the manufacturer which calculated error rate of the established connection.

Tests were performed only to variants with external antenna connector when such a variant existed for a particular model, given the external antenna's higher gain that had to be calculated and added to the actual test levels.

Adapter with short RF cable was used between the EUT and test installation.

Tests were performed in following WiFi modes:

WF111, b-mode
WF121, g-mode
WGM110, g-mode

Test setup of the WF121 and WGM110 did not allow using the slowest data rate setting so tests were performed while in g-mode.

Table 1: The test frequencies used in the tests

Frequency [MHz]:	Channel:
2412	Low
2437	Middle
2462	High

Channel 13 was not available with the monitoring software so channel 11 was used as channel high.

Test suite

Measurement/Test	Test Specification	Result
RF Output Power	EN 300 328 V.2.1.1 (2016-11)	N/T ⁽¹⁾
Power Spectral Density	EN 300 328 V.2.1.1 (2016-11)	N/T ⁽¹⁾
Duty cycle, Tx-sequence, Tx-gap	EN 300 328 V.2.1.1 (2016-11)	N/A ⁽²⁾
Accumulated Transmit Time, Frequency Occupation and Hopping Sequence	EN 300 328 V.2.1.1 (2016-11)	N/A ⁽³⁾
Hopping Frequency Separation	EN 300 328 V.2.1.1 (2016-11)	N/A ⁽³⁾
Medium Utilisation (MU) factor	EN 300 328 V.2.1.1 (2016-11)	N/A ⁽²⁾
Adaptivity	EN 300 328 V.2.1.1 (2016-11)	N/T ⁽¹⁾
Occupied Channel Bandwidth	EN 300 328 V.2.1.1 (2016-11)	N/T ⁽¹⁾
Transmitter unwanted spurious emissions in the out-of-band domain	EN 300 328 V.2.1.1 (2016-11)	N/T ⁽¹⁾
Transmitter unwanted spurious emissions in the spurious domain	EN 300 328 V.2.1.1 (2016-11)	N/T ⁽¹⁾
Receiver spurious emissions	EN 300 328 V.2.1.1 (2016-11)	N/T ⁽¹⁾
Receiver blocking	EN 300 328 V.2.1.1 (2016-11)	PASS
Geo-location capability	EN 300 328 V.2.1.1 (2016-11)	N/A ⁽³⁾
<p>Possible test case verdicts:</p> <p>Test case does not apply to the EUT: N/A EUT does meet the requirement: P (Pass) EUT does not meet the requirement: F (Fail) Test was not performed: N/T</p> <p>1) Test has been performed according to EN 300 328 V1.9.1. Details and results of the test can be found in the previous test reports that already exist for each module. 2) Not applicable to adaptive equipment 3) Not applicable to equipment using wide band modulations other than FHSS 4) Only applicable to equipment with geo-location capability</p>		

Testing location / address:

SGS Fimko Ltd
Karakaarenkuja 4
FI-02610, ESPOO
FINLAND

Receiver Blocking

Standard: EN 300 328 V.2.1.1
Tested by: EHA
Date: 3-5 April 2017
Temperature: 22 - 23 °C
Humidity: 22 - 26 %

Test result: **PASS**

Test plan

Measurements are performed according to ETSI EN 300 328 V2.1.1 clause 5.4.11.2.1

Minimum performance criteria:

Error rate of the connection shall be less than or equal to 10 % as declared by the manufacturer.

Test results

Table 2: Receiver blocking results (WF111, WF121, WGM110)

Blocking signal frequency (MHz)	Blocking signal power (dBm)	Type of blocking signal	Result
2380.0	-53	CW	PASS
2503.5	-53	CW	PASS
2300.0	-47	CW	PASS
2330.0	-47	CW	PASS
2360.0	-47	CW	PASS
2523.5	-47	CW	PASS
2553.5	-47	CW	PASS
2583.5	-47	CW	PASS
2613.5	-47	CW	PASS
2643.5	-47	CW	PASS
2673.5	-47	CW	PASS

RF-Test Equipment

Equipment	Manufacturer	Type	Inv or serial	Prev Calib	Next Calib
ATT SMAM/F 50 Ω 18 GHZ 30 DB 1 W	HUBER&SUHNER	6830.19.A	sn:RF ATTEN 09	2016-10-28	2017-10-28
ULTRA BROAD BAND POWER DIVIDER	NARDA	4426LB-4	inv:8033	2017-03-01	2018-03-01
ATTENUATOR	PASTERNAK	10dB DC-40GHz	-	-	-
SIGNAL ANALYZER	ROHDE & SCHWARZ	FSV40	inv:9093	2016-06-10	2017-06-10
RF SIGNAL GENERATOR	ROHDE & SCHWARZ	SMB100A	inv:9288	2017-02-10	2020-02-10
VECTOR SIGNAL GENERATOR	ROHDE & SCHWARZ	SMBV100A	inv:9290	2016-06-09	2019-06-09
TEMPERATURE/ HUMIDITY METER	VAISALA	HMT 333	inv:8638	2017-02-21	2018-02-21
VARIABLE ATTENUATOR	ZYSEN	ZSJ70/1-06-2A2	inv:10332	-	-